

## Technical Data

### NewColors

## Tanning Tube OH N 07/80 R

UV-Code: 80-R-27/2,7

Article No.: 45006437

**Dimensions:** See drawing (not to scale)  
**Socket:** G13 / BiPin  
**Reflector:** with reflector, type R (reflector angle 210 °)

**Electrical Data:**  
**Lamp Wattage nom.:** 80 W  
**Lamp Voltage:** 110 V  
**Lamp Current:** 0,8 A  
**Open-circuit voltage:** 230 V / 50 Hz  
**Ballast:** Ballast 80 LP  
**Starter:** OH Suncare Standard 25 - 100 W  
**Compensation:** 8,0 µF(± 10% 250V)

**Operation conditions:**  
**Cooling:** Convection  
**Burning Position:** Horizontal  
**Surrounding temperature:** 25 °C ±1 °C

**Irradiation Data:**  
**UVA Output:** 23 W  
**UVB Output:** 0,7 %  
**Sun erythema factor:\*** 0,09  
**Luminous colour:** Standard blue  
 (UVB:280-315 nm; UVA:315-400 nm)  
 $E_{er \text{ total}}^*$  27,1 mW/m<sup>2</sup>       $E_{NMSC \text{ total}}^*$  40,7 mW/m<sup>2</sup>  
 $E_{er \leq 320}^*$  16,5 mW/m<sup>2</sup>       $E_{NMSC \leq 320} / E_{NMSC > 320}^*$  2,7  
 $E_{er > 320}^*$  10,6 mW/m<sup>2</sup>       $E_{pi}^*$  15,9 W/m<sup>2</sup>

**Lifetime:**  
**Standard lifetime:** 800 h  
**Reduction of UV-intensity:** ≤ 30 % ( 315-400 nm ) after 600 h  
 Based on: 20 h - value

The data given are based on average data und has been determined by measurements made in the laborator under standard conditions. There could be minor deviations due to technical and/or physical reasons.

\* These irradiation data of a single tube have been measured in a distance of 25 cm.

\*\* Valid with 1h preageing process, 25 cm distance between tube surface and sensor, in thermal balance.

Sunbed intensity *1 (315-400 nm)	UV- *2 Device type	First *3 tanning time	Tanning time in minutes *3			MED/h Skin type 3	UV- *4 Index
			Skin type 2	Skin type 3	Skin type 4		
21 mW/cm <sup>2</sup>	II	7 min	18 min	25 min	33 min	2	9
25 mW/cm <sup>2</sup>	II	6 min	15 min	22 min	28 min	3	11
29 mW/cm <sup>2</sup>	II	5 min	13 min	19 min	24 min	3	12
33 mW/cm <sup>2</sup>	No	5 min	12 min	17 min	21 min	4	14

\*1 UVA- Sunbed intensity, measured in heighth of the skin surface; \*2 Referring DIN EN 60335-2-27; \*3 Referring DIN 5050 Part 2; \*4 Referring B

**Heraeus Noblelight GmbH**  
 Original Hanau SunCare  
 Heraeusstraße 12-14  
 D-63450 Hanau  
 Phone: +49 6181 / 35-5092  
 Fax.: +49 6181 / 35-5096  
 E-Mail: [suncare@heraeus.com](mailto:suncare@heraeus.com)  
[www.original-hanau-suncare.com](http://www.original-hanau-suncare.com)

