

## Technical Data

# MagicSun

## Tanning Tube OH M 23/160 R

UV-Code\*: 160-R-117/7,2

Article No.: 45007054

Dimensions: See drawing (not to scale)  
 Socket: G13 / BiPin  
 Reflector: with reflector, type R (reflector angle 210 °)

### Electrical Data:

Lamp Wattage nom.: 160 W  
 Lamp Voltage: 130 V  
 Lamp Current: 1,5 A  
 Open-circuit voltage: 230 V / 50 Hz  
 Ballast: Ballast 160 LP  
 Starter: OH Suncare Power 100 - 180 W  
 Compensation: 18,0 µF(± 10% 250V)

### Operation conditions:

Cooling: Convection  
 Burning Position: Horizontal  
 Surrounding temperature: 25 °C ±1°C


### Irradiation Data:

(UVB:280-315 nm; UVA:315-400 nm)

UVA Output: 46 W  
 UVB Output: 2,3 %  
 Luminous colour: Standard blue  
 te\* E<sub>NMSC</sub> total\*: 209,5 mW/m<sup>2</sup>  
 tm\* E<sub>NMSC</sub> <=320/E<sub>NMSC</sub> >320\* 7,3 mW/m<sup>2</sup>

### Lifetime:

Standard lifetime: 1.000 h  
 Reduction of UV-intensity: <= 20 % ( 315-400 nm ) after 700 h  
 Based on: 20 h - value



The data given are based on average data und has been determined by measurements made in the labor under standard conditions. There could be minor deviations due to technical and/or physical reasons.

Heraeus reserves the right to alter the illustrations and technical data in this Technical Data Sheet. The latest up version of the Technical Data Sheet is prevailing. It is within the customer' s responsibility to check whether he is possession of the latest updated version of the Technical Data Sheet."

\* These irradiation data of a single tube have been measured in a distance of 25 cm.

\*\* Valid with 1h preageing process, 25 cm distance between tube surface and sensor, in thermal bala

Sunbed intensity UVA <sup>1</sup>	UV-Device Type <sup>2</sup>	Recommended first exposure time <sup>3</sup> t <sub>e</sub>	Recommended max. exposure time <sup>3</sup> t <sub>m</sub>
30 mw/cm <sup>2</sup>	No	2 Minutes	9 Minutes
35 mw/cm <sup>2</sup>	No	1 Minutes	7 Minutes
40 mw/cm <sup>2</sup>	No	1 Minutes	6 Minutes
46 mw/cm <sup>2</sup>	No	1 Minutes	6 Minutes

<sup>1</sup> UVA-Sunbed intensity, measured in height of the skin surface

<sup>2</sup> Referring to IEC 60335-2-27

<sup>3</sup> Referring to FDA 21 CFR 1002

Heraeus Noblelight GmbH · Original Hanau SunCare  
 Heraeusstraße 12-14 · D-63450 Hanau  
 Phone: +49 6181 / 35-5092 Fax.: +49 6181 / 35-5096  
 E-Mail: suncare@heraeus.com \* www.original-hanau-suncare.coi

Heraeus Noblelight LLC · 2150 Northmont Parkway, Suite L  
 GA 30096 USA - Duluth · United States  
 Phone: +1 770 418 0707\* Fax.: +49 6181 / 35-5096  
 E-Mail: tanning@noblelight.ne · www.original-hanau-suncare.com/us



31.05.2005