

## Technical Data

### NewColors

## Tanning Tube OH N 100 T F73 RDC

UV-Code\*: 100-O-48/8,4

Article No.: 80006923

Dimensions: See drawing (not to scale)  
 Socket: RDC - F73  
 Reflector: without reflector, type O (reflector angle )

### Electrical Data:

Lamp Wattage nom.: 100 W  
 Lamp Voltage: 120 V  
 Lamp Current: 1,0 A  
 Open-circuit voltage: 230 V / 50 Hz  
 Ballast: Ballast 100 LP  
 Starter: OH Suncare Standard 25 - 100 W  
 Compensation: 10,0  $\mu$ F ( $\pm$  10% 250V)

### Operation conditions:

Cooling: freibrennend  
 Burning Position: Horizontal  
 Surrounding temperature: 25 °C  $\pm$ 1°C


### Irradiation Data:

(UVB:260-320 nm; UVA:320-400 nm)

UVA Output: 28 W  
 UVB Output: 4,7 %  
 Luminous colour: Standard blue  
 te\*: 145 min  $E_{\text{NMSC total}^*}$ : 88,1 mW / m<sup>2</sup>  
 tm\*: 420 min  $E_{\text{NMSC} \leq 320 / E_{\text{NMSC} > 320^*}$ : 8,4 mW / m<sup>2</sup>

### Lifetime:

Standard lifetime: 800 h  
 Reduction of UV-intensity:  $\leq$  30 % ( 320-400 nm ) after 600 h  
 Based on: 20 h - value



The data given are based on average data und has been determined by measurements made in the laboratory under standard conditions. There could be minor deviations due to technical and/or physical reasons.

Heraeus reserves the right to alter the illustrations and technical data in this Technical Data Sheet. The latest updated version of the Technical Data Sheet is prevailing. It is within the customer's responsibility to check whether he is in possession of the latest updated version of the Technical Data Sheet."

\* These irradiation data of a single tube have been measured in a distance of 25 cm.

\*\* Valid with 1h preageing process, 25 cm distance between tube surface and sensor, in thermal balance.

Sunbed intensity <sup>1</sup> UVA	UV-Device Type <sup>2</sup>	Recommended first exposure time <sup>3</sup> t <sub>e</sub>	Recommended max. exposure time <sup>3</sup> t <sub>m</sub>
21 mw/cm <sup>2</sup>	No	2 Minutes	10 Minutes
25 mw/cm <sup>2</sup>	No	2 Minutes	8 Minutes
29 mw/cm <sup>2</sup>	No	1 Minutes	7 Minutes
33 mw/cm <sup>2</sup>	No	1 Minutes	6 Minutes

<sup>1</sup> UVA-Sunbed intensity, measured in height of the skin surface

<sup>2</sup> Referring to IEC 60335-2-27

<sup>3</sup> Referring to FDA 21 CFR 1002

Heraeus Noblelight LLC \* 2150 Northmont Parkway, Suite L  
 GA 30096 USA - Duluth \* United States  
 Phone: +1 770 418 0707 \* Fax.: +49 6181 / 35-5096  
 E-Mail: tanning@noblelight.net \* www.original-hanau-suncare.com/us



07.11.2006